



# ALCHEMIST Series

Adiabatic subcooler for CO<sub>2</sub>





## THE NEW ALCHEMIST SERIES



**Alchemist** is a simple and compact PATENTED product, designed to **increase chillers' power and seasonal energy efficiency**, specifically for retrofitting. Alchemist has been developed by MITA cooling technologies for commercial refrigeration (food-storage), a particular and demanding sector, focused on efficiency and reliability.

The adiabatic subcooler designed by MITA increases the efficiency in the commercial refrigeration, without alteration to general plant configura-

tion: it's **ONLY** necessary to intercept fluid coming from condensers and to design Alchemist electrical and water connections.

When installing the adiabatic sub-cooler? In all the cases where there is a refrigeration system for supermarkets. Available a range for Commercial Refrigeration, CO<sub>2</sub> plants (R744): Refrigeration capacity from approximately 50 [kWf] to 500 [kWf], depending on the needs and the size of the shop.




## ADIABATIC SUBCOOLING

**Alchemist** combines the **adiabatic cooling** physical principle, together with **the refrigerant fluid subcooling**.


The adiabatic cooling consists in air temperature reduction through humidification. **Adiabatically treated air subcools the liquid** coming from chiller condenser circulating inside the machine's coils.

**Alchemist** is a plug & play product that, in comparison with other evaporative/adiabatic solutions used for increasing efficiency, **maintains the existing chiller configuration and plant layout**.

### Plug & Play



*Example with refrigerant R744 (CO<sub>2</sub>).  
Frigorific circuit beneficial effect (yellow part) thanks to the Alchemist introduction (sub-cooling)*



*Cooling effect*

## SPECIFICATIONS

- ◆ **Support structure** made of press-folded galvanized metal sheets and subsequently protected by a RAL 7016 epoxy paint cycle.
- ◆ **Heat exchange coil** arranged inside the cooler, made of copper pipes and aluminium fins. Angle between coil, diameter of pipes, thickness and pitch of fins are designed to offer the best heat exchange performance with reduced fluid and airflow pressure drops.
- ◆ **Flocked PVC humidifier pack.** The geometric configuration allows the use of untreated water. The particular flocked pack design, as opposed to other types of adiabatic packs, requires spraying only for short periods at long intervals of time: this minimizes the power and optimises water consumption. The adiabatic pack is easily accessible and removable for cleaning.

- ◆ **Temperature probes** for measuring external air, refrigerant, humidified air temperature inside the machine.
- ◆ **Aluminium air Inlet grille** (removable in an easy way), for the adiabatic section protection: avoiding direct penetration of light and water splashes during the wetting cycles.
- ◆ **EC Plug Fan**
- ◆ **Command and control panel** of the various functions of the cooler, with the possibility of data transmission via MODBUS TCP/IP.
- ◆ **Wetting water collection gutters** in stainless steel AISI 304,


accessible and cleanable. The machine is totally accessible in a simple, fast and safe way.



- ◆ The unit does not require special maintenance.
- ◆ System provides for the direct use of mains water. Generally, the quantity of water is minimal and limited to the summer season at a preset threshold. This topic has been given particular


attention both in the choice of components in direct contact and in the management of the water itself: no accumulations, no stagnation.

*The unit is totally accessible, in a simple, fast and safe way*





# OPERATION



The **PATENTED Alchemist Series** is fully automated and managed by an operator panel integrated with the possibility of **remote management**: just set the subcooling temperature you wish to obtain and the system will self-adjust optimising energy and water consumption.

There are **two operating ways**: dry and adiabatic.

**Dry operation**: external air is drawn in and conveyed onto the finned coils.

**The humidification process is deactivated**, no water is present and the humidifier pack is dry.

The subcooling readings by temperature probes modulate fan speed to **optimise power consumption**.



**Adiabatic operation**: external air is drawn in and passed through the humidifier pack (protected inside the machine). The adiabatically cooled air (therefore at a lower temperature than the external air) is conveyed to the finned coils thus **increasing the frigorific fluid subcooling**.



The subcooling readings by temperature probes modulate fan speed and adiabatic cycles to **minimise power/water consumption**.



# MAIN ADVANTAGES

- ◆ *High savings kWh of produced frigorific energy*
- ◆ *Plug & Play solution, with integrated control system*
- ◆ *Easy and simple access for maintenance*
- ◆ *Compact design, modularity and easy installation*
- ◆ *EC Plug fan technology*
- ◆ *Available software to have ROI & VAN*

*Simulation: Alchemist in a 160 kWf plant with parallel compression*



*Alchemist in a supermarket*



# WHERE TO USE ALCHEMIST


*HFC frigorific circuits retrofitting*

*In combination with new HFC or HFO chillers*

*Transcritical plants with CO<sub>2</sub>*



# FLOW, POWER, NOISE LEVELS, CONSUMPTIONS AND DIMENSIONS



Model*	CO <sub>2</sub> flow (kg/hr)	Thermal power (kW)	CO <sub>2</sub> Pressure loss (bar)	Instant consumption (l/h)	Electrical consumption (A)	Dimensions B / A / H (mm)
Alchemist 5000 S.R.	6000	32	0,6	58	2,80	2231 / 1615 / 1732
Alchemist 4000 S.R.	4500	24	0,6	51	2,80	2231 / 1365 / 1483
Alchemist 3000 S.R.	3500	18	0,6	38	3,65	2231 / 1265 / 1383
Alchemist 2500 S.R.	2500	13	0,6	13	2,10	2231 / 1115 / 1233
Alchemist 1500 S.R.	2000	11	0,6	11	0,80	887 / 729 / 997
Alchemist 1000 S.R.	1100	6	0,6	6	0,80	683 / 561 / 767

\* Available also other dedicated solutions

## Data valid for the following conditions:


T<sub>in</sub> CO<sub>2</sub> (°C) 38

P<sub>in</sub> CO<sub>2</sub> (bar) 94


ΔT subcool. (°C) 4

T<sub>amb</sub> (°C) 35

H.R. (%) 40



Design for models from 2500 S.R. to 5000 S.R.



Design for models 1000 S.R. and 1500 S.R.



Via del Benessere, 13  
27010 Siziano (PV) - Italy  
+39 0382.67599 - info@mitact.it

